

Dry-Break Couplings

DRY-BREAK COUPLINGS

CERTIFICATES/APPROVALS

- TÜ.AGG.162-93 (ADR, RID, IMDG and TA-Luft)
- European directives 97/23/EC (PED)
- 94/9/EC (ATEX) compliant
- EN ISO 9001:2008
- ISO 14001 certificate
- OHSAS 18001:2007

FEATURES

- Extremely reliable and simple single action operation
- Safe transfer of hazardous or high value liquid products
- Minimal residual loss on disconnection
- Lock pin feature (2" to 4") standard
- In-built swivel adaptor for hose unit
- Easy servicing

TECHNICAL DETAILS

- Materials: Stainless Steel 316L, other on request
- Seals: FKM (Viton®), other on request
- Working pressure: PN 25 (test pressure: PN 37.5)
- End connections: BSP threads, other on request
- Compatibility: NATO STANAG 3756

www.trelleborg.com/fluidhandling

Contact: tes.serviceclients@trelleborg.com

HOSE UNIT			
Sizes	BSP threads	Code no.	Stock
25	1"	5105392	✓
50	2"	5105393	✓
80	3"	5105394	✓
100	4"	5105395	✓



TANK UNIT			
Sizes	BSP threads	Code no.	Stock
25	1"	5105396	✓
50	2"	5105397	✓
80	3"	5105398	✓
100	4"	5105399	✓

