



CAMLOCK

V04/09/2016

TECHNICAL INFORMATION

- CAMLOCK according to MIL-C 27487
DIN282/NF EN 14420-7 2013
- Shank according to EN 14420-2
- Material: stainless steel 316/1.4401
- Working pressure: 16 bar
- Temperature: -20°C +65°C
- NBR gasket



RELATED PRODUCTS

- UTS ferrules
- Safety clamps
- Other gasket: FPM/EPDM/
FEP-Silicone/FPM-PTFE

www.trelleborg.com/fluidhandling

Contact: robin.lallemand@trelleborg.com



CAMLOCK - TYPE C - COUPLER SS316

Female - NBR gasket

Part number	Coupling size (mm)	DN Hose (mm)	Stock
5105269	3/4"	19	✓
5103409	1"	25	✓
5105270	1" 1/4	32	✓
5103410	1" 1/2	38	✓
5103411	2"	50/51	✓
5103412	2" 1/2	63	✓
5103413	3"	75-76	✓
5103414	4"	100/102	✓

CAMLOCK - TYPE E - ADAPTER SS316

Male

Part number	Coupling size (mm)	DN Hose (mm)	Stock
5105267	3/4"	19	✓
5103397	1"	25	✓
5105268	1" 1/4	32	✓
5103398	1" 1/2	38	✓
5103399	2"	50/51	✓
5103400	2" 1/2	63	✓
5103401	3"	75-76	✓
5103402	4"	100/102	✓

