



Fact Sheet: Conductive

The Dartex® Conductive range is widely used for applications where the prevention of static build-up is crucial, such as x-ray tables, medical scanners and operating theatres.

Key benefits

The Dartex® Conductive range is designed with anti-static technology and tested for electrical resistance to BS2040/A.4.1.

- **Dissipates static build-up** from medical diagnostic equipment, e.g. scanners and x-rays
- Suitable for use in **operating theatres**
- **Maintains anti-static properties** for the lifetime of the product

Breathability – the moisture vapor transmission (MVT) properties of PU keeps skin cool and dry, unlike PVC which doesn't 'breathe'

Stretch & Recovery – essential for pressure redistribution and the prevention of avoidable pressure injuries

Easily cleaned – either wipe clean or machine washable.

PVC FREE

Recommended cleaning

GENERAL GUIDANCE

Always follow the manufacturer's washing instructions. Ask for a copy of the Dartex® Support Surfaces cleaning guidance for further information on compatible chemicals.

- **Protect** by removing spillages promptly with an absorbent dry cloth. General soiling can be handled with a microfibre cloth and tepid, soapy water (non alkaline) to remove the spillage

- **Rinse** with clean water and dry with a soft absorbent cloth. Bodily fluids should be removed promptly (within 15 minutes) with cold water then cleaned as above
- **Dry** thoroughly before returning to use or storage.

Why choose Trelleborg Engineered Coated Fabrics?

We are specialist manufacturers of polyurethane-coated technical textiles for medical applications.

All PU fabrics provide a fluid-proof, virus-proof barrier for infection control. Our

industry leading Dartex® range combines unique stretch and recovery capabilities with breathable, high quality PU coatings, to provide pressure redistribution¹ around the world.

Contact our technical sales team for specifications and more information:

✉ TIS.ECF.healthmed@trelleborg.com 🌐 trelleborg.com/engineered-coated-fabrics
 📧 TrelleborgHM 📱 trelleborg-healthcare-&-medical

	2-way & 4-way stretch No delamination
	71°C & 95°C Machine washable Dyed and Scour fabrics available No delamination
	Bio-compatibility (ISO10993-5) Cytotoxicity = < Grade 1 (ISO10993-10) Skin Irritation – classed as non-irritant; Skin Sensitisation – considered to be non-sensitiser
	Eco flame retardant: Crib 5 BS6807, sources 0, 1 & 5 conforms when used with a suitable combustion modified foam RoHS Directive 2011/65/EU compliant
	Fungistatic Contains an anti-fungal / anti-microbial agent to control microbial deterioration; The products do not contain any nano materials
	MVP (g/m ² /24hours) Payne Cup ASTM D1653: 400-600 ASTM E96 method BW: 100
	Waterproof Water penetration resistance/ Hydrostatic head (kPa) 35 minimum; typical 100 (BS3424-26)
	Weldable Polyester and Nylon fabric options available
	Wipe clean For infection control
	UV Printable Innovative, no odour ink that does not crack when stretched – 5 colour print process

References:
¹ Haxby, R; Pearce, K; Turton, T; Scott, I; Williams, C. (2019). Support Surface Cover & Core: Working Together in Sweet Harmony. Available for download <https://www.trelleborg.com/en/engineered-coated-fabrics/industries/healthcare-and-medical>